

CE conformity

Allied Vision standard cameras are manufactured in accordance with the CE standard and its underlying directions.

Contacting Allied Vision

Ordering and general information:

<http://www.alliedvision.com/en/contact>
info@alliedvision.com

Telephone

EMEA: +49 36428-677-0
The Americas: +1 978-225-2030
Asia-Pacific: +65 6634-9027
China: +86 (21) 64861133

Support:

support@alliedvision.com

Software installation (all models)

Allied Vision provides the Vimba SDK (software development kit), free of charge.

<http://www.alliedvision.com/en/products/software>

Software installation (CL models)

The software highly depends on the frame grabber type used. A software development kit (SDK) and a demo soft-

ware for first live preview is usually provided by the frame grabber manufacturer.

Hardware installation (CL models)

The installation procedures depend on the used Camera Link frame grabber. Refer to the documentation of the grabber manufacturer.

For more information on the Camera Link interface, see the camera technical manuals.

<http://www.alliedvision.com/en/support/technical-documentation>

For accessories like cables or power supply see:

<http://www.alliedvision.com/en/contact>

Environmental conditions

The conditions listed below are applicable to all **Goldeye G** and **CL** models:

- Operation (ambient temperature): -20 °C to +55 °C
- Storage: - 20 °C to +70 °C
- Relative humidity: 10 % to 95 % non-condensing

For more information and other camera families, refer to the technical manuals:

<http://www.alliedvision.com/en/support/technical-documentation>

Camera safety notifications

There are no switches or parts inside the camera that require adjustment. The warranty becomes void upon opening the camera casing.

If the product is disassembled, reworked or repaired by unapproved service personnel, Allied Vision or its suppliers cannot be held responsible for the subsequent performance or quality of the camera.

The camera does **not** generate dangerous voltages internally.

Copyright

All text, pictures and graphics are protected by copyright and other laws covering intellectual property. It is prohibited to copy or modify them for trade use or transfer, or inclusion on web sites.

Allied Vision Technologies GmbH 02/2016

Headquarters:

Allied Vision Technologies GmbH
 Taschenweg 2a
 D-07646 Stadtroda / Germany

All rights reserved.

Managing Director: Mr. Frank Grube

Tax ID: DE 184383113



Cleaning precautions

- Mount/remove lenses and filters in a **dust-free environment**, and **do not** use compressed air (which can force dust into cameras and lenses).
- Use only **optical quality tissue**/cloth if you must clean a lens or filter.
- Read: **Installation Manual**, Chapter *Cleaning instructions*.



Power supply precautions

Use only DC power supplies with insulated cases or a protective ground conductor and a connector suitable to your power outlet.